


1/2 [13] X 4 [102] PULL SLOT W/
 Ø1/4 [6] CENTER PIN (2 PLACES)

2X Ø5/8 [16] THRU HOLE
 W/ Ø1 1/4 [32] X 1/2
 [13] DEEP COUNTERBORE

NOTES:

1. LOGO TO BE SPECIFIED: _____
2. FURNISHED W/(2) 3/8-7 X 4 [102] LONG S.S. HEX HEAD AUGER BOLTS & (2) Ø3/8 [10] S.S FLAT WASHERS.
3. THIS COVER IS RATED FOR A STATIC DESIGN LOAD OF 15,000 LBS. [66,720 N] OVER A 10 [254] X 10 [254] AREA AND MUST PASS A MIN. STATIC TEST LOAD OF 22,500 LBS. [100,080 N].

DIMENSIONS ARE IN INCHES OR MILLIMETERS IN BRACKETS UNLESS OTHERWISE NOTED.



DATE	BY	PLATE	WEIGHT	REV
10/11/99	K3P6	10/11/99	126# 30kg	1C S
10/17/99				G
10/18/99				9/12
			HUBBELL 1001 INDUSTRIAL PARK DR LENEXA, KANSAS 66042 WWW.HUBBELL.COM	
QUAZITE® 24 X 36 COVER STANDARD VERSION			DRAWING DESCRIPTION QUAZITE® 24 X 36 COVER STANDARD VERSION	
PROJECT NUMBER 99527			DRAWING NUMBER PG2436HS00	
SHEET 1 OF 1			REV G	