



1/2 [13] X 4 [102] PULL SLOT
W/ Ø1/4 [6] CENTER PIN
4 PLACES

Ø5/8 [16] THRU. HOLE
W/ Ø1 1/4 [32] X 1/2 [13]
DEEP COUNTERBORE (2 PLACES)



NOTES:

1. LOGO TO BE SPECIFIED: _____
2. THIS COVER IS RATED FOR A STATIC DESIGN LOAD OF 15,000 LBS. [66,720 N] OVER A 10 [254] X 10 [254] AREA AND MUST PASS A MIN. STATIC TEST LOAD OF 22,500 LBS. [100,080 N].
3. FURNISHED W/(2) 3/8-7 [10] X 4 [102] LONG HEX HEAD AUGER BOLTS AND (2) Ø3/8 [10] FLAT WASHERS.
4. DIMENSIONS IN BRACKETS ARE IN MILLIMETERS UNLESS OTHERWISE SPECIFIED.



DIMENSIONS ARE IN INCHES OR MILLIMETERS IN BRACKETS UNLESS OTHERWISE NOTED.		WEIGHT		LOC
DATE	BY	NO.	DESCRIPTION	
12/27/95	W/93	208#	QUAZITTE COVER	S
12/28/95	M/97	94kg		E
12/28/95	M/97	B		3/12

USER OR PROJECT NUMBER	SHEET	OF	DRAWING NUMBER
95551	1	1	PG3048HS00



QUAZITTE® COVER