



NOTES:

1. LOGO TO BE SPECIFIED: _____
2. THIS COVER IS RATED FOR A STATIC DESIGN LOAD OF 22,500 [100,080 N] OVER A 10 [254] X 20 [508] AREA. MUST PASS A MINIMUM STATIC TEST LOAD OF 33,750 [150,120 N].
3. FURNISHED W/ (2) 1/2-6 X 2 1/2 [64] LONG HEX HEAD AUGER BOLTS, AND (2) Ø1/2 [13] WASHERS.

DIMENSIONS ARE IN INCHES OR MILLIMETERS IN BRACKETS UNLESS OTHERWISE NOTED.

REV	DATE	BY	CHKD	APP'D	DESCRIPTION
1	8/17/01	JCS	JCS	MCS	QUAZITTE COVER
2	8/17/01				
3	8/17/01				
4	8/17/01				

ITEM NO.	PROJECT NUMBER	SHEET	OF	DRAWING NUMBER
01416		1	1	PG3660HH00