



NOTES:

1. LOGO TO BE SPECIFIED: _____
2. FURNISHED W/ (8) 1/2-13 UNC X 4 [102] LONG S.S. HEX HEAD BOLTS, (8) Ø1/2 [13] S.S. FLAT WASHERS & (3) PIECES OF 6 [152] X 4 [102] STRUCTURAL TUBING.
3. THIS COVER IS RATED FOR A STATIC DESIGN LOAD OF 22,500 LBS. [100,085 N] OVER A 10 [254] X 20 [508] AREA AND MUST PASS A MIN. STATIC TEST LOAD OF 33,750 LBS. [150,128 N].

DIMENSIONS ARE IN INCHES OR MILLIMETERS IN BRACKETS UNLESS OTHERWISE NOTED.		WEIGHT		DRAWING DESCRIPTION		REVISIONS	
BY	DATE	1210#	549kg	QUAZITE® 48 X 96 X 03 COVER		IC	S
CHKD	8/5/03	549kg	549kg	STANDARD VERSION		C	11/04
APPR		B					
PROJECT NUMBER		PROJECT		DRAWING NUMBER			
03653		1 - 02 - 1		PG4896HH00			

03653

PG4896HH00