




PCORE
ELECTRIC

KV CLASS	345 kV	BIL	1175 kV	Uy	220 kV
CURRENT RATING					
4000 AMP BOTTOM CONN. TRANSFORMER 4500 AMP BOTTOM CONN. OIL CIR. BREAKER					
MIN. CREEP	345.00 [8763.0]	MIN. STRIKE	115.0 [2921.0]		
CREEP/L-G	1.73 [44.0]	STD.	IEEE C57.19.00/01		
PCB CONTENT OF OIL IS LESS THAN 1 ppm					


DWG.	CATALOG NUMBER	GLAZE COLOR
SD	POC1175B4000S	BROWN
SD	POC1175G4000S	LT. GRAY
TITLE		
POC BUSHING		
TRANSFORMER — BREAKER INTERCHANGEABLE SILVER PLATED BRASS TOP TERMINAL		

DATE	9-4-03	REV. DATE	9-22-15
MAXIMUM ALTITUDE	10000 ft [3000 m]		
NET WEIGHT	1423 lb [645 kg]		
ANGLE OF INCLINATION FROM THE VERTICAL	0° TO 60°		




MOUNTING FLANGE

ALIGNMENT BETWEEN HOLES
IN BOTTOM TERMINAL & IN
FLANGE COINCIDE WITHIN ±2°



**ALIGNMENT OF FLANGE
AND BOTTOM TERMINAL
TOP VIEW**



BOTTOM END CAP

DIMENSIONS IN INCHES [MILLIMETERS]

REVISION UPDATED FORMAT, CREEP/L-G WAS CREEP/Uy, OIL CIR. BREAKER CURRENT RATING WAS 4000A, REV. BOTTOM CAP DETAIL

SCALE 1/1

NOTE TO PURCHASER:
ALL SALES OF PCORE PRODUCTS ARE SUBJECT
TO OUR STANDARD TERMS AND CONDITIONS
AND THE LIMITED WARRANTIES THEREUNDER