

6

5






4

3

2

1

CATALOG NUMBER	COLOR	DESCRIPTION
REKFP	IVORY	FIBER BRACKET



SECTION A-A

## NOTES:

1. KIT CONTAINS ONE FIBER BRACKET.
2. SURFACE FINISH: IVORY.
3. SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE.

Created on AUTOCAD

DIMENSIONING AND TOLERANCE PER  
ANSI Y14.5M-1982  
UNLESS OTHERWISE SPECIFIED,  
DIMENSIONS ARE IN INCHES (MM).  
TOLERANCES  
.XX = ±.01 (.25)  
.XXX = ±.005 (.127)  
.XXXX = ±.0025 (.0635)  
ANGLE TOL ±1°

IN ACCEPTING OUR DRAWINGS,  
BLUEPRINTS, OR SUPPORTING  
DOCUMENTATION FOR QUOTATION  
OR OTHER PURPOSES, YOU AGREE  
NOT TO DISCLOSE TO OTHERS  
THE IDEAS, INFORMATION, OR  
DESIGNS SHOWN HEREIN, AND  
THAT YOU WILL MAKE NO USE  
OF SAME WITHOUT PERMISSION

PROJECT REFERENCE:  
N/AMATERIAL:  
16 GA C.R.S.DRAWN BY:  
D.O'CONNOR 7/16/04

CHECKED BY:

APPROVED BY:



Hubbell Premise Wiring  
HUBBELL INCORPORATED (Delaware)  
14 Lord's Hill Road, Stonington, Connecticut 06378

TITLE: FIBER BRACKET

SIZE DRAWING NO.

C C11401

REV.

A

SCALE: 1/1 SHEET 1 OF 1

REV.	ECN	DATE	DESCRIPTION	CHG BY	APPD BY
A	5352	7/16/04	INITIAL RELEASE	DPO	