


CATALOG NUMBERING DESCRIPTION




M = MADE IN USA ONLY
 T = MADE ANYWHERE
 AMP RATING (SEE TABLE)

TYPE T FUSELINK
 TA - WITH SOLID HEAD
 TA - WITH REMOVABLE HEAD

PACKING OPTION:
 BP

OPTIONS:
 FOR TA TYPE FUSELINKS
 W/SUFFIX 23 = 23" LG (OVERALL LENGTH)
 W/SUFFIX 24 = 24" LG (OVERALL LENGTH)
 W/SUFFIX 25 = 25" LG (OVERALL LENGTH)
 W/SUFFIX 26 = 26" LG (OVERALL LENGTH)
 W/SUFFIX 27 = 27" LG (OVERALL LENGTH)
 W/SUFFIX 28 = 28" LG (OVERALL LENGTH)
 W/SUFFIX 29 = 29" LG (OVERALL LENGTH)
 W/SUFFIX 30 = 30" LG (OVERALL LENGTH)
 W/SUFFIX 31 = 31" LG (OVERALL LENGTH)

CATALOG NUMBER EXAMPLE



AMP RATING	'A' DIA.	'B' DIA.	'C' DIA.	'D' DIA.	'L' DIM
1 THRU 20	.50	.75	.311	.090	5-1/2
25	.50	.75	.311	.125	5-1/2
30 THRU 50	.50	.75	.311	.141	5-1/2
65	.75	.75	.431	.203	5-1/2
80 THRU 100	.75	.75	.431	.234	5-1/2
140	1.00	1.00	.460	.290	6
200	1.00	1.00	.563	.406	6

CHANCE
 TOLERANCE CHART
 EC 73658 DTD 5/17/18

CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS, INC. NO REPRODUCTION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS, INC. HUBBELL POWER SYSTEMS UNPUBLISHED WORKS ARE RESERVED UNDER THE COPYRIGHT LAWS.

HUBBELL POWER SYSTEMS

FUSE LINKS, TYPE T
 SOLID & REMOVABLE HD

DO NOT SCALE THIS DRAWING

REV A

CAT / PART / ASST NO.
 PSSATFUSELINK SEE CHART

DWN BY CLARK DATE 04-02-07 SHEET 01 OF 01