



PIG TAIL	COPPER	SEE DRAWING
CABLE MANAGEMENT	STEEL	GALVANIZED
STAB-IT CLAMP	STEEL	GALVANIZED
STUD BRACKET	STEEL	GALVANIZED
FASTENERS	STEEL	GALVANIZED
SIDE	STEEL	GALVANIZED
SPACER	STEEL	GALVANIZED
DESCRIPTION	MATERIAL	FINISH

LIST OF PARTS THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE	
TITLE:	4" SQ BOX W/ FAR SIDE SUPPORT, STUD BRACKETS, & STAB-IT™ CLAMP

TOLERANCE UNLESS OTHERWISE SPECIFIED .XX DECIMAL ±.015 .XXX DECIMAL ±.005 ANGLE ±2°			
	DRAWN BY:	RMV	SCALE
	APP. BY:	N.S.	
	DATE:	11-08-23	



- NOTES:
1. ALL DIMENSIONS ARE IN INCHES AND [MILLIMETERS]
 2. VOLUME: 30.3 IN³ [496.5 CM³]
 3. UL LISTED
 4. FOR INSTRUCTION SHEET SCROLL DOWN TO NEXT SHEET


INSTRUCTION SHEET

4" & 4 -11/16" SQUARE BOXES WITH "G" BRACKET

STUD MOUNTING


STEP 1

Place box over stud at an angle as shown





STEP 2

Push it until it snaps into place and attach it with (2) screws (not included)



STEP 3


Install mud ring (not included)



SIDE BY SIDE STUD MOUNTING


STEP 1

Place box over stud as shown below





STEP 2

Push it until it snaps into place and attach it with (2) screws (not included)



STEP 3


Install mud rings (not included)



BRACE MOUNTING (TO BE USED ONLY WITH BRACE #9030G)


STEP 1

Insert bracket on brace as shown below



STEP 2

Push it until it snaps into place and attach it with (2) screws (not included)



STEP 3

Install mud ring (not included)

