



LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
SPACER	STEEL	GALVANIZED
SIDE	STEEL	GALVANIZED
CLAMPS	STEEL	GALVANIZED
STUD BRACKET	STEEL	GALVANIZED
FAR SIDE SUPPORT	STEEL	GALVANIZED
FASTENERS	STEEL	GALVANIZED

248HWP CUS

INITIAL RELEASE	RMV	01-02-18
SYM.	REVISION DESCRIPTION	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE:  
**4" SQ. BOX, 2-1/8" DP., 1/2"-3/4" KO'S, W/ FAR SIDE SUPPORT, MC CLAMPS, & STUD BRACKET**

TOLERANCE UNLESS OTHERWISE SPECIFIED

.XX DECIMAL ±.015  
 .XXX DECIMAL ±.005  
 ANGLE ±2°

**RACO**

South Bend, Indiana

DRAWN BY:	RMV	SCALE:
APP. BY:	N.S.	1:3
DATE:	01-02-18	

248HWP

DIMENSION SHEET FOR CAT. NO.

SIZE:

**A**

11in\*17in

NOTES:

1. ALL DIMENSIONS ARE IN INCHES AND [MILLIMETERS]
2. BOX VOLUME: 30.3 IN<sup>3</sup> [496.5 CM<sup>3</sup>]
3. UL LISTED
4. KNOCKOUTS IN LOCATION "E" ARE ACCESSIBLE FOR 5-1/2" [140] & 6" [152.4] STUDS ONLY

KNOCKOUTS		
TRADE SIZE	LOCATION	QTY.
(1/2"-3/4") TKO®	B, D	1
1/2" KO	B, D	2
1/2" KO	E	1