



- NOTES:
1. ALL DIMENSIONS ARE IN INCHES AND [MILLIMETERS]
 2. BOX VOLUME: 42 IN³ [688.2 CM³]
 3. ACCEPTS ALL 4-11/16" COVERS, 707RAC AND 709 PARTITIONS, ALL SOLD SEPARATELY
 4. UL LISTED

KNOCKOUTS		
TRADE SIZE	LOCATION	QTY.
(1/2"-3/4") TKO®	A, B, C, D, E	3
1/2" KO	E	1

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
SPACER	STEEL	GALVANIZED
SIDE	STEEL	GALVANIZED
FASTENERS	STEEL	GALVANIZED

INITIAL RELEASE	RMV	01-29-18	
SYM.	REVISION DESCRIPTION	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE: **ASSEMBLY: 4-11/16" SQ X 2-1/8" DP WELDED BOX WITH RAISED GROUND**

TOLERANCE UNLESS OTHERWISE SPECIFIED
 .XX DECIMAL ±.015
 .XXX DECIMAL ±.005
 ANGLE ±2°

RACO
 South Bend, Indiana

DRAWN BY:	RMV	SCALE:
APP. BY:	N.S.	1:3
DATE:	01-29-18	

257 CUS

DIMENSION SHEET FOR CAT. NO. 257, 8257, 8257SP

SIZE: **A**

11in*17in