


REVISIONS			
REV.	DATE	DESCRIPTION	BY
-	11-01-22	INITIAL RELEASE	RMV



- NOTES:
1. ALL DIMENSIONS ARE IN INCHES AND [MILLIMETERS]
 2. BOX VOLUME: 47.8 IN³ [783.3 CM³] (14.5 IN³ [237.6 CM³] PER GANG)
 3. UL LISTED

KNOCKOUTS		
TRADE SIZE	LOCATION	QTY.
1/2"-3/4" CONCENTRIC KO	A, C, E	3
1/2"-3/4" CONCENTRIC KO	B	2
1/4" PRI-OUTS	E	6

DESCRIPTION	MATERIAL	FINISH
BRACKET	STEEL	GALVANIZED
SIDE	STEEL	GALVANIZED
SPACER	STEEL	GALVANIZED

LIST OF PARTS

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE:
3 GANG BOX, 2 1/2" DP., W/ FM LONG BRACKET

	TOLERANCE UNLESS OTHERWISE SPECIFIED .XX DECIMAL ± .015 .XXX DECIMAL ± .005 ANGLE ± 2°	DRAWN BY: RMV APP. BY: N.S. DATE: 11-01-22	SCALE: 1:4	SIZE: A
--	---	--	------------	---------