


REVISIONS			
REV.	DATE	DESCRIPTION	BY
-	11-01-22	INITIAL RELEASE	RMV



DESCRIPTION	MATERIAL	FINISH
BRACKET	STEEL	GALVANIZED
SIDE	STEEL	GALVANIZED
SPACER	STEEL	GALVANIZED

**LIST OF PARTS**

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE:  
**4 GANG BOX, 2 1/2" DP., W/ FM LONG BRACKET**

KNOCKOUTS		
TRADE SIZE	LOCATION	QTY.
1/2"-3/4" CONCENTRIC KO	A, C, E	4
1/2"-3/4" CONCENTRIC KO	B	2
1/4" PRI-OUTS	E	8

- NOTES:
- ALL DIMENSIONS ARE IN INCHES AND [MILLIMETERS]
  - BOX VOLUME: 63.5 IN<sup>3</sup> [1040.6 CM<sup>3</sup>] (14.5 IN<sup>3</sup> [237.6 CM<sup>3</sup>] PER GANG)
  - UL LISTED

TOLERANCE UNLESS OTHERWISE SPECIFIED  
.XX DECIMAL ± .015  
.XXX DECIMAL ± .005  
ANGLE ± 2°



DRAWN BY:	RMV	SCALE:	SIZE:
APP. BY:	N.S.		
DATE:	11-01-22	1:4	<b>A</b>