



BRACKET MAY BE BENT TO ACOMODATE THINNER BLOCK

DETAIL A
SCALE 1 : 1

- NOTES:
1. ALL DIMENSIONS ARE IN INCHES AND [MILLIMETERS]
 2. BOX VOLUME: 22.5 IN³ [368.7 CM³]
 3. ACCEPTS #676 PARTITION , SOLD SEPARATELY
 4. ACCEPTS # 701FG GANGABLE PROTECTOR PLATE , SOLD SEPARATELY
 5. UL LISTED

OUTSIDE DIMENSIONS				
GANG NO.	A		B	
	INCH	MM	INCH	MM
1	3.29	83.6	1.94	49.2
2	5.10	239.5	3.75	95.25
3	6.91	175.5	5.56	141.2
4	8.73	221.7	7.38	187.5
5	10.54	267.7	9.20	233.7
6	12.35	313.7	11.0	279.4

KNOCKOUTS -SINGLE GANG BOX	
TRADE SIZE	LOCATION
1/2", 3/4" TKO®	2- TOP 2- BOTTOM 2- BACK 2- EACH SIDE

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
GANGABLE SPACER	STEEL	GALVANIZED
SIDES	STEEL	GALVANIZED
BLOCK LOC™ BRACKETS	STEEL	GALVANIZED
FASTENERS	STEEL	GALVANIZED

SYM.	REVISION DESCRIPTION	APP	DATE
	INITIAL RELEASE	K.K.	

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE:
**BLOCK LOC™
3-1/2" DEEP GANGABLE
MASONRY BOX**

TOLERANCE UNLESS OTHERWISE SPECIFIED .XX DECIMAL ±.015 .XXX DECIMAL ±.005 ANGLE ±2°	RACO South Bend, Indiana		SCALE: B 1:2
	DRAWN BY:	K.K.	
	APP. BY:	N.S.	
	DATE:	1/26/2015	