



- NOTES:
1. ALL DIMENSIONS ARE IN INCHES AND [MILLIMETERS]
 2. BOX VOLUME: 22.5 IN³ [368.7 CM³]
 3. ACCEPTS #676 PARTITION, SOLD SEPARATELY
 4. ACCEPTS # 701FG GANGABLE PROTECTOR PLATE, SOLD SEPARATELY
 5. UL LISTED

OUTSIDE DIMENSIONS		
GANG NO.	A	
	INCH	MM
1	1.94	49.2
2	3.75	95.25
3	5.56	141.2
4	7.38	187.5
5	9.20	233.7
6	11.0	279.4

KNOCKOUTS -SINGLE GANG BOX	
TRADE SIZE	LOCATION
1/2", 3/4" TKO®	2- TOP
	2- BOTTOM
	2- BACK
	2- EACH SIDE

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
GANGABLE SPACER	STEEL	GALVANIZED
SIDES	STEEL	GALVANIZED
FASTENERS	STEEL	GALVANIZED

INITIAL RELEASE	K.K.		
SYM.	REVISION DESCRIPTION	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE: **3-1/2" DEEP GANGABLE MASONRY BOX**

TOLERANCE UNLESS OTHERWISE SPECIFIED		RACO South Bend, Indiana	SCALE: B
.XX DECIMAL ±.015	.XXX DECIMAL ±.005		
ANGLE ±2°		DRAWN BY: K.K.	
		APP. BY: N.S.	
		DATE: 1/26/2015	

FILE NAME: 689 CUS

DIMENSION SHEET FOR CAT. NO. 689

SIZE: B