



BRACKET MAY BE BENT TO ACOMODATE THINNER BLOCK

DETAIL A
SCALE 1 : 1

- NOTES:
1. ALL DIMENSIONS ARE IN INCHES AND [MILLIMETERS]
 2. BOX VOLUME: 45.0 IN³ [737.4 CM³]
 3. ACCEPTS # 971 PARTITION , SOLD SEPARATELY
 4. ACCEPTS # 701FG GANGABLE PROTECTOR PLATE , SOLD SEPARATELY
 5. UL LISTED

KNOCKOUTS -SINGLE GANG BOX	
TRADE SIZE	LOCATION
1/2", 3/4" CONC. KO'S	4- TOP
	4- BOTTOM
	4- BACK
	2- EACH SIDE

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
SPACER	STEEL	GALVANIZED
SIDES	STEEL	GALVANIZED
BLOCK LOC™ BRACKETS	STEEL	GALVANIZED

SYMBOL	REVISION DESCRIPTION	APP	DATE
	INITIAL RELEASE	K.K.	

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE: **BLOCK LOC™ TWO GANG 3-1/2" DEEP WELDED MASONRY BOX**

TOLERANCE UNLESS OTHERWISE SPECIFIED .XX DECIMAL ±.015 .XXX DECIMAL ±.005 ANGLE ±2°	RACO South Bend, Indiana		SCALE: 1:2
	DRAWN BY:	K.K.	
	APP. BY:	N.S.	
	DATE:	1/26/2015	