



8-32 X 1/2"
PHILLIPS / SLOT
DRIVE (FASTENER) X 2

- NOTES:
1. ALL DIMENSIONS ARE IN INCHES AND [MILLIMETERS]
 2. BOX VOLUME: 21 IN³ [344.1 CM³]
 3. UL LISTED

KNOCKOUTS		
TRADE SIZE	LOCATION	QTY.
1/2"	A	3
1/2"	B, C, D	2
(1/2"-3/4") TKO®	A	2
(1/2"-3/4") TKO®	B, C, D	1

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
SPACER	STEEL	GALVANIZED
SIDE	STEEL	GALVANIZED
FS BRACKET	STEEL	GALVANIZED
FASTENERS	STEEL	GALVANIZED

INITIAL RELEASE OF DRAWING	RMV	11-06-17
SYMBOL	REVISION DESCRIPTION	APP DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE:
4" SQUARE WELDED BOX 1.50" DEEP WITH FS BRACKET

TOLERANCE UNLESS OTHERWISE SPECIFIED
 .XX DECIMAL ±.015
 .XXX DECIMAL ±.005
 ANGLE ±2°

RACO
 South Bend, Indiana

DRAWN BY: RMV
 APP. BY: N.S.
 DATE: 11-03-17

SCALE: 1:3

197 CUS

DIMENSION SHEET FOR CAT. NO. **197 & 8197**

SIZE: **A**