


REVISIONS			
REV.	DATE	DESCRIPTION	BY
-	05-03-24	INITIAL RELEASE	RMV



WIRE	COPPER	SEE DRAWING
SPADE TERMINAL	BRASS	N/A
GROUND SCREW	STEEL	ANODIZED GRN
DESCRIPTION	MATERIAL	FINISH

LIST OF PARTS

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE:
PIGTAIL, 8" LONG, #12 AWG GREEN INSULATED STRANDED WIRE, WITH GROUND SCREW AND SPADE TERMINAL

TOLERANCE UNLESS OTHERWISE SPECIFIED .XX DECIMAL ± .015 .XXX DECIMAL ± .005 ANGLE ± 2°			DRAWN BY:	RMV	SCALE:	SIZE:
			APP. BY:	N.S.		
	DATE:	05-03-24	1:2	A		

NOTES:
1. ALL DIMENSIONS ARE IN INCHES AND [MILLIMETERS]