


-NOTES-

1. ALL STEEL CONSTRUCTION
2. HOT DIP GALVANIZED PER ASTM A-153- (LATEST REVISION).
3. DESIGNED TO FIT 6-1/2" TO 11-1/2" DIA. POLES.
4. ORDER 1/2" EYENUT, CAT. NO. 6500, AND 1/2" MACH. BOLTS FOR USE WITH LIFTING HOLES.
5. FOR GROUNDING PURPOSES, ORDER GROUND CLAMP CAT. NO. C212-0140.
6. DESIGN TESTED TO 2000 LBS. LOAD PER TRANSFORMER POSITION WITH SIMULTANEOUS LOADING 14' OUT FROM MOUNTING PLATES.



VIEW OF LIFTING EYE
CAT. NO. T212-0222

CAT. NO. C212-0141

LATEST EC NO:		REV.	DATE	CHANGED BY	RESP ENGINEER
92102006		B	03-03-93	QUALLS	ODOM
					DO NOT SCALE THIS DWG THIRD ANGLE PROJECTION ISO DUAL DIMENSIONS IN=INCH, MM=MILLIMETER
DRN BY:	DATE	TITLE:		SIZE	
QUALLS	03-03-93	"T" TYPE TRANSFORMER MOUNTING RACK		C	
				DWG NO: SA212-0141	

CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL / A. B. CHANCE COMPANY. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT WRITTEN CONSENT BY HUBBELL / A. B. CHANCE COMPANY. © 2000 HUBBELL/A. B. CHANCE. UNPUBLISHED - ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS