






CAT. NO.	DESCRIPTION	"D"	"L"	NO. PER BOX
C6CS06A	6" BRACKET 6" T-SLOT	6	6	4
C6CS08A	6" BRACKET 8" T-SLOT	6	8	6
C6CS12A	6" BRACKET 12" T-SLOT	6	12	10
C6CS24A	6" BRACKET 24" T-SLOT	6	24	10



- NOTES -

1. ALL BRACKET MATERIAL IS ALUMINUM. BOLTS, NUTS AND WASHERS ARE GALVANIZED STEEL.
2. BRACKET AVAILABLE WITH NO T-SLOT OR WITH STANDARD LENGTH 12, 24, 36 INCH 4-WAY T-SLOT.

CHANCE
TOLERANCE CHART

CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.



HUBBELL POWER SYSTEMS

TITLE

BRACKET
CONDUIT STANDOFF

SIZE	DWG NO.	CAT / PART / ASSY NO.	REV
SB	SAC6CS06A	SEE CHART	--
DO NOT SCALE THIS DRAWING	DRN BY BERGER	DATE 12/10/12	SHEET 01 OF 01