






NOTES :

- 1.) MATERIAL: STEEL, HOT DIP GALVANIZED PER ASTM A153 (LATEST REVISION).
- 2.) BOLT AND NUT ASSEMBLY MEETS THE ANSI MINIMUM TENSILE LOAD OF 12,400 LBS. AND THE 180° BEND TEST.

CATALOG NUMBER	DESCRIPTION	"A"	"B"
PSHB580125	MACH OR CROSSARM BOLT	1.25	1.25
PSHB580150	MACH OR CROSSARM BOLT	1.50	1.50
PSHB580175	MACH OR CROSSARM BOLT	1.75	1.50
PSHB580200	MACH OR CROSSARM BOLT	2.00	1.50
PSHB580225	MACH OR CROSSARM BOLT	2.25	1.50
PSHB580250	MACH OR CROSSARM BOLT	2.50	1.50
PSHB580300	MACH OR CROSSARM BOLT	3.00	1.50
PSHB580350	MACH OR CROSSARM BOLT	3.50	1.50
PSHB580400	MACH OR CROSSARM BOLT	4.00	3.00

LATEST EC NO: 27351		REV.:	DATE 07/08/08	CHANGED BY LURKINS	RESP ENGINEER LURKINS
DO NOT SCALE THIS DWG			THIRD ANGLE PROJECTION		 ISO DUAL DIMENSIONS IN=INCH, MM=MILLIMETER
					
DRN BY: JUL	DATE 07-08-08	TITLE: 5/8" HEX HEAD BOLTS			SIZE B
				 DWG NO: SAPSHB580125	

CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL / A.B. CHANCE COMPANY. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT WRITTEN CONSENT BY HUBBELL / A.B. CHANCE COMPANY. © 2001 HUBBELL/A.B. CHANCE. UNPUBLISHED - ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS