



**SHORT CIRCUIT STICK
4 CLAMPS**

**CATALOG NO.
PST6003583**

IEC 61230 RATING: 3kA / 1sec ($\leq 1000V$)

CONDUCTOR RANGE: 3.5mm - 19.5mm

EPOXIGLAS DIA: 26.99mm
ELECTRICALLY TESTED PER ASTM F711
AND IEC 60855

NOTE-2

PART NUMBER	ITEM	DESCRIPTION	QTY
P403-1396	1	HANDLE	1
PSP4033770	2	STORM GUARD, 1-1/16"	1
PSP6003558	3	GRIPPER	4
PSZ0012444	4	RIVET, 3/16"	4
PSZ0012447	5	COMPRESSION SPRING	4
P001-0248	6	PIN, 0.187" X 1.312"	4
PSP6003593	7	CHANNEL, 32" LONG	1
PSP4004344	8	POLE, 1-1/16" X 48"	1
PSP6003595	9	POLE CAP, 1-1/16"	1

CHANCE



HUBBELL POWER SYSTEMS, INC.

CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS

TITLE SHORT CIRCUIT STICK, 4 CLAMPS			
SIZE C	DWG NO. SAPST6003583	CAT / PART / ASSY NO. PST6003583	REV A
DO NOT SCALE THIS DRAWING	DRN BY BSU	DATE 12/18/18	SHEET 1 OF 1