



- NOTES-
1. ALL STEEL CONSTRUCTION.
  2. HOT DIP GALVANIZED PER ASTM A-153-(LATEST REVISION).
  3. ORDER 5/8" EYENUT, CAT. NO. 6502, AND 5/8" MACH. BOLTS FOR USE WITH LIFTING HOLES.
  4. FOR GROUNDING PURPOSES, ORDER GROUND CLAMP CAT. NO. C212-0140.
  5. DESIGN TESTED TO 5000 LBS. LOAD PER TRANSFORMER POSITION WITH SIMULTANEOUS LOADING 14" OUT FROM MOUNTING PLATES.
  6. STENCIL "ABC 3000 LBS" IN TALL LETTERS ON MOUNTING PLATE.

CAT. NO. T212-0193

6- 5/8 X 2-1/2 & 6- 3/4 X 2-1/2 MOUNTING BOLTS FURNISHED

<b>CHANCE</b> TOLERANCE CHART		<b>HUBBELL POWER SYSTEMS</b> POWER SYSTEMS, INC.	
CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED. ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.			
TITLE <b>"TT" TYPE TRANSFORMER MOUNTING RACK</b>		SIZE C SAT2120193	CAT / PART / ASSY NO. T212-0193
DO NOT SCALE THIS DRAWING	DRN BY JMK	DATE 01/29/13	REV - SHEET 1 OF 1