


| | |
|--|------------------------------------|
| CATALOG NUMBER | C600-2231 |
| ELECTRICAL RATINGS | |
| CONTINUOUS CURRENT (AMPS) | 400 |
| FAULT CURRENT-15 CYCLES (AMPS) | 43000 |
| FAULT CURRENT-30 CYCLES (AMPS) | 30000 |
| MECHANICAL RATINGS | |
| RECOMMENDED TORQUE-CLAMP (IN.-LB.) | 250 |
| RECOMMENDED TORQUE-SET SCREW (IN.-LB.) | 60 |
| MAINLINE RANGE-MAX. | 1-1/2" THK ANGLES- 1-1/2" THK FLAT |
| MAINLINE RANGE-MIN. | 1/8" |
| JUMPER RANGE-MAX. | 4/0 GND CABLE W/ THREADED STUD |
| JUMPER RANGE-MIN. | #2 GND CABLE W/ THREADED STUD |
| WEIGHT EACH | 2 LB. / 0.9 KG. |
| ASTM DESIGNATION | TYPE 1 / CLASS B / GRADE 5 |
| IEC RATING (15 CYCLES) | |
| JAWS | SERRATED |
| FERRULE | THREADED |

| | | | |
|--|-----------------------------|---|--------------------------------------|
| CHANCE TOLERANCE CHART | |  HUBBELL® POWER SYSTEMS <small>POWER SYSTEMS, INC.</small> | |
| <small>CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED. ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.</small> | | TITLE CLAMP FLAT FACE | |
| | | <small>SIZE</small> SB | <small>DWG NO.</small> SA600-2231 |
| <small>DO NOT SCALE THIS DRAWING</small> | <small>DRN BY</small> QUALL | <small>DATE</small> 10/24/00 | <small>SHEET 1 OF 1</small> |