



SL.NO	CATALOG NO.	DESCRIPTION
1	K6P28	MULTIPLE SERVICE CONNECTOR
2	K6PC28	POLYETHYLENE INSULATING COVER
3	K6P28C	CONNECTOR AND COVER ASSEMBLY

REV	DATE	DESCRIPTION	ECO	BY	C'H'K
A	11/20/2012	SALES DRAWING REDRAW IN INVENTOR	29218	YM	MB



5/8-18X5/8"LG. BRASS
SOCKET SET SCREWS



1.31 WITH MAX. CONDUCTOR IN PLACE
[33] BEFORE COMPRESSION

CAST COPPER ALLOY

NOTES:

1. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.
2. ACCOMMODATES: SIX #6 (.184 [5] DIA.) TO 4/0 (.528 [13] DIA.) INSULATED CU. CABLES.

TO ORDER BURNDY® PRODUCTS CALL		INSULATED MULTIPLE SERVICE CONNECTOR	
UNITED STATES		ITEM NO: 210025	
1-800-346-4175 (LONDONDERRY, NH)		CAT. NO: K6P28C	
CANADA:		DRAWN BY: RHS 05/12/1965	
1-800-361-6975 (QUEBEC)		CHECKER: ERD 05/15/1965	
1-800-387-6487 (ALL OTHER PROVINCES)		DSN APRVL: --	
FOR PRODUCT INFO: http://www.burndy.com		MFG APRVL: --	
		QA APRVL: JAMES 04/15/2013	
		MKT APRVL: HALL 04/12/2013	
		PROJ #: --	
		SIZE: B	
		DRAWING NO: SD058772-01	
		REV: A	
		SHEET 1 OF 1	