


DRAWING NO.
SD016087-01

CATALOG NUMBER	L	NUMBER OF OUTLETS
ZMTDN2-20	9.06 [230]	2
ZMTDN4-20	12.56 [319]	4
ZMTDN6-20	16.06 [408]	6
ZMTDN8-20	19.56 [497]	8
ZMTDN10-20	23.06 [586]	10
ZMTDN12-20	26.56 [675]	12
ZMTDN14-20	30.06 [764]	14
ZMTDN16-20	33.56 [852]	16

REV.	DATE	DESCRIPTION	ECO	BY	C'K'D.
B	3/12/09	TYP. ADDED MISSING #1.500 VALUE	17734	PL	PL



NOTES:

1. OUTLETS MAY BE EITHER "A" OR "B" SIZE.
OUTLET SIZE: A = 600 kcmil (.893)
B = 1000 kcmil (1.152)
2. WHEN SUPPLIED WITH "B" SIZE OUTLET, CATALOG NUMBER TO HAVE "B" ADDED TO END.
3. MATERIAL: INSERT AND STUD CLAMPING ELEMENT - COPPER ALLOY
INSULATION - DIATEX
MOLE™ INSERT - COPPER ALLOY
4. FINISH: METAL PARTS: ELECTRO TIN PLATED
5. CAPACITY: 2000 AMPERES
6. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS, ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.

REFERENCE: FD39318

TO ORDER BURNDY® PRODUCTS CALL
UNITED STATES:
1-800-346-4175 (LONDONDERRY, NH)
CANADA:
1-800-361-6975 (QUEBEC)
1-800-387-6487 (ALL OTHER PROVINCES)
FOR PRODUCT INFO: <http://www.fciconnect.com>

TO ORDER BURNDY PRODUCTS CALL 1-800-346-4175
MANCHESTER, NH 03109, USA
FOR PRODUCT INFO = <http://www.fciconnect.com>

STUD MOLE™	
ITEM NO:	N/A
CAT NO:	ZMTDN--20 (TABLE)
SCALE:	1/1
DRAWN BY:	M.G. 3/13/47
CHECKER:	L.H. 3/20/47
DSN APPVL:	--
MFG APPVL:	--
QC APPVL:	--
MKT APPVL:	--
PROD FAM:	--
PROJECT #:	--
DOCUMENT TYPE:	Sales
REL LEVEL:	AutoCAD
DRAWING NO	SD016087-01
REV	B
SHEET 1 OF 1	

