

CONDUCTOR			BOLT SIZE	CATALOG NO.	FIG. NO.	DIMENSIONS							BURNDY INSTALLATION TOOLING (# CRIMPS)					DIELESS (# CRIMPS)	WIRE STRIP LENGTH					
FLEX	CODE (AWG)	NAVY				B	C	H	K	L	N	O.D.	T REF.	Z MIN.	DIE INDEX	COLOR CODE	MECHANICAL RATCHET			HYDRAULIC				
															MD7-34R MD6	OUR840	Y750 Y35 Y39	Y46 $\triangleleft$ 4	Y45 $\triangleleft$ 3					
4/0 AWG CLASS G-M DLO (550/24)	4/0 AWG	200	1/4	YAG28L-TC14-LD	1	1.03 [26]	1.14 [29]	---		2.26 [57]		.77 [20]	.15 [4]		15	PURPLE	W28RT (2) X28CRT (3) W28CVT (2)	X28CRT (3) W28CVT (2)	U28RT UR420SWE (1)	U28RT UR420SWE (1)	U28RT UR420SWE (1)	MECHANICAL: MY29-11 (1)	HYDRAULIC: Y644(1) PAT644(1) Y81KFT(1) PAT81KFT(1)	1/16"
				YAG28L-TC14-LD-45	2		1.72 [44]	.27 [7]	2.13 [54]	.31 [8]		.33 [8]												
				YAG28L-TC14-LD-90	3		1.87 [47]		1.14 [29]															
			5/6	YAG28L-TC516-LD	1			---		2.32 [59]				15	PURPLE								1/16"	
				YAG28L-TC516-LD-45	2		1.72 [44]	.33 [8]	2.19 [56]	.34 [9]		.36 [9]												
				YAG28L-TC516-LD-90	3		1.87 [47]		1.21 [31]															
			3/8	YAG28L-TC38-LD	1			---		2.45 [62]				15	PURPLE								1/16"	
				YAG28L-TC38-LD-45	2		1.72 [44]	.40 [10]	2.32 [59]	.41 [10]		.42 [11]												
				YAG28L-TC38-LD-90	3		1.87 [47]		1.33 [34]															
			1/2	YAG28L-TC12-LD	1			---		2.70 [69]				15	PURPLE								1/16"	
				YAG28L-TC12-LD-45	2		1.72 [44]	.53 [13]	2.57 [65]	.53 [13]		.55 [14]												
				YAG28L-TC12-LD-90	3		1.87 [47]		1.58 [40]															
			5/8	YAG28L-TC58-LD	1			---		2.95 [75]				15	PURPLE								1/16"	
				YAG28L-TC58-LD-45	2		1.72 [44]	.69 [17]	2.82 [72]	.66 [17]		.67 [17]												
				YAG28L-TC58-LD-90	3		1.87 [47]		1.83 [46]															
4/0 AWG CLASS G-M DLO (550/24)	4/0 AWG	200	3/4	YAG28L-TC34-LD	1	1.03 [26]	1.14 [29]	---		3.14 [80]		.77 [20]	.15 [4]		15	PURPLE	W28RT (2) X28CRT (3) W28CVT (2)	X28CRT (3) W28CVT (2)	U28RT UR420SWE (1)	U28RT UR420SWE (1)	U28RT UR420SWE (1)		1/16"	
				YAG28L-TC34-LD-45	2		1.72 [44]	.81 [21]	3.00 [76]	.75 [19]		.77 [19]												
				YAG28L-TC34-LD-90	3		1.87 [47]		2.02 [51]															

SEE SHEET 1 OF 18 FOR NOTES

TO ORDER BURNDY® PRODUCTS CALL  
 UNITED STATES:  
 1-800-346-4175 (LONDONDERRY, NH)  
 CANADA:  
 1-800-361-6975 (QUEBEC)  
 1-800-387-6487 (ALL OTHER PROVINCES)  
 FOR PRODUCT INFO: <http://www.burndy.com>

HYLUG™	
ITEM NO: N/A	
CAT NO: YAG28L-TC-LD-	
SCALE: N/A	
DRAWN BY: D.FILLION 12/17/92	
CHECKER: KAY HENRY 12/18/92	
DSN APPVL: PALAGI/HESKEY 12/22/92	
MFG APPVL: ---	
QC APPVL: A LLOYD 12-31-92	
MKT APPVL: T NELSON 01/12/93	
PROD FAM: ---	
PROJECT #: 00 52410	SIZE
DOCUMENT TYPE: Sales	D
REL LEVEL: AutoCAD	
DRAWING NO	REV
SE208132	B
SHEET 10 of 18	

REV.	DATE	DESCRIPTION	ECO	BY	C*K'D.
B	05/20/2015	REMOVED "C" FROM CATALOG NUMBERS	40318	MA	RM