

DRAWING NO.
SE209341

REV.	DATE	DESCRIPTION	ECO	BY	C'K'D.
0	01/10/95	ADD NEW SHEET PER ECO.	2147	JWA	JL

EPP..EC-LG SERIES 1/2 HORSEPOWER

CATALOG NUMBER	DESCRIPTION	OPERATING OUTPUT PRESSURE
EPP10EC-LG	SMALL ELECTRIC HYDRAULIC PUMP, REMOTE ROCKER CONTROL SWITCH, 1/2 HP. 115VAC MOTOR	10,000 PSI
EPP8EC-LG	SMALL ELECTRIC HYDRAULIC PUMP, REMOTE ROCKER CONTROL SWITCH, 1/2 HP. 115VAC MOTOR	8,800 PSI
EPP6EC-LG	SMALL ELECTRIC HYDRAULIC PUMP, REMOTE ROCKER CONTROL SWITCH, 1/2 HP. 115VAC MOTOR	6,000 PSI


EPP..EC-LG SERIES ELECTRI HYDRAULIC PUMP	
ITEM NO: ---	
CAT NO: EPP..EC-LG (TABLE)	
SCALE: N/A	
DRAWN BY: R. PERREAU 12/16/94	
CHECKER: N. PRESSMAN 12/16/94	
DSN APPV: J. LEFAVOUR 12/16/94	
MFG APPV: ---	
QC APPV: ---	
MKT APPV: D. HAMILTON 12/16/94	
PROD FAM: ---	
PROJECT #: ---	
DOCUMENT TYPE: ---	
REL LEVEL: ---	

TO ORDER BURNDY® PRODUCTS CALL

UNITED STATES:
1-800-346-4175 (LONDONDERRY, NH)

CANADA:
1-800-361-6975 (QUEBEC)
1-800-387-6487 (ALL OTHER PROVINCES)

FOR PRODUCT INFO: <http://www.burndy.com>



DRAWING NO	REV
SE209341	0
SHEET 4 OF 4	