



REV.	DATE	DESCRIPTION	ECO	BY	C'K'D.
B	5/26/08	CHNG'D LEVER TO KNOB	16169	PL	RP



NOTES:

1. READ AND FOLLOW ALL INSTRUCTIONS PROVIDED BY THE OPERATOR'S MANUAL AND WARNING LABELS BEFORE USING THIS TOOL.
2. DIMENSIONS IN [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED. DIMENSIONS ARE FOR REFERENCE ONLY.

SPECIFICATIONS

WEIGHT: 4.5 LBS. [2.0 KG].

JAWS:

PATENTED HIGH STRENGTH STEEL, AND REPLACEABLE. YIELDING MINIMUM CONDUCTOR DISTORTION.

HANDLES:

FIBERGLASS WITH COMFORT GRIP DESIGN AND ERGONOMIC HANDLE ENDS PROVIDES A POSITIVE ANTI-SLIP GRIP.

FIBERGLASS HANDLE MATERIAL MEETS OR EXCEEDS ASTM F711. (100 kv/ft. DIELECTRIC STRENGTH)

TYPE OF MECHANISM:

HAND DRIVEN RATCHET WITH RAPID ADVANCE

CUTTING CAPACITY	
!WARNING DO NOT CUT ENERGIZED LINE OR ACSR	
COPPER – 1000 kcmil	
ALUMINUM – 1000 kcmil	
MAX. INSUL. DIA. – 2.375 IN. [60.0]	

TO ORDER BURNDY® PRODUCTS CALL		RATCHET CABLE CUTTER – HAND TOOL	
UNITED STATES: 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: 25015089	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT NO: RCC1000	
FOR PRODUCT INFO: http://www.burndy.com		SCALE: N/A	
		DRAWN BY: D DOBRINSKI 2/5/98	
		CHECKER: D DOBRINSKI 3/18/98	
		DSN APPVL: G HESKEY 3/4/98	
		MFG APPVL: ---	
		QC APPVL: S GRAY 3/4/98	
		MKT APPVL: B HARGROOVE 3/4/98	
		PROD FAM: ---	
		PROJECT #: ---	
		DOCUMENT TYPE: Sales	
		REL LEVEL: AutoCAD	
		DRAWING NO: SE211271-01	
		SHEET 1 OF 1	

