


NOTES:

1. MATERIAL: BODY, KEEPER, SOCKET EYE – GALVANIZED DUCTILE IRON.
CLEVIS PIN, U-BOLT, NUT, WASHER – GALVANIZED STEEL.
COTTERS – #302 STAINLESS STEEL
3. DIMENSIONS IN INCHES.
4. HOT DIP GALVANIZE PER ASTM A153
5. WEIGHT 12.35 LBS
6. SAG EYE ULT. STRENGTH IS 18K LBS
7. RATED SLIP STRENGTH ON STANDARD SHIELD WIRE CABLES IS 40% RBS (PARTIAL TENSION).
FOR MANY SHIELD WIRE CABLES, MINIMUM SLIP STRENGTH IS 60% (NORMAL TENSION).
CONSULT FACTORY FOR SLIP STRENGTH TEST DATA ON SPECIFIC CABLE SIZES.
8. MAY BE USED TO DEADEND COPPER OR COPPERWELD PHASE CONDUCTORS. MAGNETIC INDUCTION HEATING WILL OCCUR.



CLAMPING RANGE:
ø0.36 – ø0.84

ANDERSON TOLERANCE CHART		HUBBELL® POWER SYSTEMS	
CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.		TITLE STRAIN CLAMP	
SIZE B		30K LBS ULT BODY STR	
DWG NO. CUTSHEET		CAT / PART / ASSY NO. SWDE84S	
DO NOT SCALE THIS DRAWING		REV A	
DRN BY KMK		DATE 11/16/16	
SHEET 1		OF 1	