

.44X1.0
SLOT (4X)

DIAGRAM LABEL


TERMINAL SCREWS ARE
COMBINATION 8-32
PHIL-SLOT WITH SEMS

SECONDARY SIDE 7.82 PRIMARY SIDE

SERIES/PARALLEL
JUMPER (2X)


IDENTIFICATION
LABEL

TRANSFORMER SPECIFICATIONS	
PRIMARY VOLTAGE(S)	240/347/380
SECONDARY VOLTAGE(S)	120x240
RATED V.A.	3000
RATED FREQUENCY	50/60
INSULATION CLASS	180°C @ MAX RISE 115°C
AGENCY APPROVALS	UL, CUL
ESTIMATED WEIGHT	53 LBS



CONNECTION DIAGRAM

DIMENSIONS ARE IN INCHES TOLERANCES: .XX ± .03 .XXX ± .010 ANGULAR: ± 1°	DRAWN BY:	VS	DATE	06/08/2020
	CHECKED BY:			
	SOURCE	N/A		
	MATERIAL	N/A		
FINISH	N/A			PROPRIETARY AND CONFIDENTIAL THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF ACME ELECTRIC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF ACME ELECTRIC IS PROHIBITED.
DO NOT SCALE DRAWING				

 Acme Electric	
DESCRIPTION: <h1>3000 VA</h1>	
SIZE DWG. NO. A TB3000N012	
WEIGHT:	LBS.
SHEET 1 OF 1	