


- MOUNTING BOARD: 3/4" EXTERIOR GRADE TREATED PLYWOOD, STANDARD.
- DOORS: STANDARD DOUBLE SWINGING DOORS WITH STAINLESS STEEL LIFT-OFF HINGES, 3-POINT LOCKING HANDLE. DOORS HAVE BRACKETS, WHICH HOLD THEM IN THE OPEN POSITION.
- MATERIAL: ALUMINIUM,
- LOUVER: 4" LOUVERS WITH SCREENS (STANDARD).
- GROUND LUG: AL-CU LUG FURNISHED (STANDARD).
- BOARD SIZE: 29" X 35"
- OUTDOOR METER, INSTRUMENT TRANSFER & SUBSTATION EQUIPMENT ENCLOSURES, NEMA 3R

				TO ORDER CMC PRODUCTS		DRAWN BY: TS		NAME OF PART:		CAT. NO.:	
				UNITED STATES 1-513-860-4455		11-26-20		INSTRUMENT TRANSFER & SUBSTATION EQUIPMENT ENCLOSURE		BA123238DD	
				CANADA 1-800-361-6975		CHECKED BY:		DWG NO:		A	
				MEXICO 011-52-722-265-4400				UB22700351-S			
A NEW DRAWING CREATED				11-26-20 TS		DRAWING NOT TO SCALE			SHEET NO: 1 OF 1		
REV.	DESCRIPTION			ECN	DATE	INIT.					

THIS INFORMATION IS PROPRIETARY TO CONNECTOR MFG. CO. AND IS NOT TO BE DISCLOSED OUTSIDE OF CONNECTOR MFG. CO. WITHOUT A CONFIDENTIALITY AGREEMENT



CONNECTOR MANUFACTURING CO.

HAMILTON, OHIO