


M-6782 4

PORTION OF PLUG FROM X-X TO Y-Y REPOSITIONABLE IN 90° INCREMENTS.



NOTES:

1. THIS DEVICE IS NOT WATERTIGHT.
2. SHIPPED WITH COVER, CORD GRIP & CONTACT CARRIER UNASSEMBLED.
3. TERMINAL WIRE CAPACITY #4 AWG MAX. (#12 AWG MAX) FOR PILOT CONTACT.
4. COLOR, RATING & CONTACT CONFIGURATION WITH RESPECT TO INDEX KEY OF DEVICE FROM DATUM X-X TO Y-Y IS COMPATIBLE WITH I.E.C. 309.
5. PILOT CONTACT RATING A-600 (MAKE 7200VA, BREAK 720 VA MAX)
6. CORD CAPACITY - 1.25 MAX. .75 MIN. DIA-ROUND CORD.

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
HOUSING	NYLON	
COVER	NYLON	
CORD CLAMP	NYLON	
CONTACT CARRIER	POLYESTER	
CONTACT	BRASS	
ASS'Y. SCREWS	STAIN. ST.	
TERMINAL SCREW	STAIN. ST.	

CATALOG NUMBER	CLOCK POSITION	RATING	COLOR CONT. SHROUD	PILOT CONT.	UL	CSA	CATALOG NUMBER	CLOCK POSITION	RATING	COLOR CONT. SHROUD	PILOT CONT.	UL	CSA
							A460P9		60A-3Ø 250V	BLUE	NO	YES	YES
							A460P9M4		60A-3Ø 250V	BLUE	YES	YES	YES
							A560P9		60A 3ØY 120/208V	BLUE	NO	YES	YES
A360P6		60A-250 V.A.C.	BLUE	NO	YES	YES	A460P12		60 AMP 125/250V	ORANGE	NO	YES	YES

SUPERSEDES DWG. DATED 7-13-89

SYM	REVISIONS	APP	DATE
4	ADDED A560P9 PER DCN12059 RCM	RDK	11/11/04
3	ADDED A360PG PER DCN2088 RMM	M.M.	6-24-93
2	REVISED & REDRAWN AL	M.M.	12-13-89

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE.

TITLE  
60 AMP. PIN & SLEEVE  
ANGLE PLUG

TOLERANCES UNLESS OTHERWISE SPECIFIED	WIRING DEVICE DIVISION HARVEY HUBBELL, INC. BRIDGEPORT, CONN.	
FRACTIONS ± 1/64	DR. BY <u>A.J.L.</u>	APP. BY _____
DECIMALS ± .005	TR. BY _____	SCALE <u>1</u>
ANGLES ± 2°	CHK'D. BY _____	DATE <u>12-13-89</u>

CODE 74545

DIMENSION SHEET FOR CAT. NO. SEE CHART  
 REPAIRABLE  NON-REPAIRABLE   
 B M-6782 4