


M-13402 1



CAT. NO.	AFGF20TRW	AFGF20TRI	AFGF20TRLA	AFGF20TRGY	AFGF20TRBK	AFGF20TR
COLOR	WHITE	IVORY	LIGHT ALMOND	GRAY	BLACK	BROWN

- NOTES:
- 20A-125V RECEPTACLE (NEMA 5-20R)
20A-125V FEED THRU.
 - DIMENSION FORMAT: INCHES [Millimeters]

DEVICE VOLUME	MEASUREMENT (IN^3)
IN BOX (FROM STRAP, BACK)	4.34
TOTAL	5.35

LIST OF PARTS		
DESCRIPTION	MATERIA	FINISH

REPAIRABLE NON-REPAIRABLE

1	INITIAL RELEASE PER DCN 22053 JZW	NB	4-22-16
SYM	DESCRIPTION	APPRO	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE	CUSTOMER DRAWING 20A AF/GFI
-------	--------------------------------

TOLERANCES UNLESS OTHERWISE SPECIFIED	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT	
FRACTIONS ±1/64	DR. BY JZW	APP. BY NB
DECIMALS ±005	TR. BY	SCALE N/A
ANGLES ±2'	CHK'D BY NB	DATE 4/22/2016

DIMENSION SHEET FOR CAT. NO.

B
M-13402
1