


M-11868 2

| GENERAL INFORMATION | | | |
|---------------------|--------------|------------|-----------------|
| WIRE LOCATION | WIRE | WIRE COLOR | WIRE SIZE (AWG) |
| 1 | - | - | - |
| 2 | - | - | - |
| 3 | GROUND (G) | GREEN | #12 |
| 4 | - | - | - |
| 5 | NEUTRAL (N1) | WHITE | #12 |
| 6 | LINE (L1) | BLACK | #12 |
| 7 | - | - | - |
| 8 | - | - | - |

NOTES:
 1. RATING: 20A 120/208 V.
 2. ALL DIMENSIONS ARE IN INCHES [mm] EXCEPT THE FLEXIBLE METAL CONDUIT LENGTH IN FOOT.

LIST OF PARTS

| DESCRIPTION | MATERIAL | FINISH |
|------------------|---------------|------------|
| MALE CONNECTOR | THERMOPLASTIC | BLACK |
| FEMALE CONNECTOR | THERMOPLASTIC | BLACK |
| CONDUIT | GALV. STEEL | |
| CLAMP | STEEL | ZINC PLATE |
| RIVET | STEEL | ZINC PLATE |
| INSULATOR | THERMOPLASTIC | |
| WIRE | COPPER | |



DIMENSION SHEET FOR CAT. NO. REPAIRABLE NON-REPAIRABLE
 SEE TABLE
 B
 M-11868
 2

| SYM | REVISIONS | APP | DATE |
|-----|----------------------------------|-----|---------|
| 2 | UPDATE THE PRINT PER DCN #21027. | | 2/5/15 |
| 1 | NEW RELEASE PER DCN #20674 | | 6/17/14 |

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

| | | | |
|---------------------------------------|--------------|--|-------------|
| TOLERANCES UNLESS OTHERWISE SPECIFIED | | WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT | |
| .XX = ±.01 | .XXX = ±.005 | DR. BY DMP | APP. BY |
| ANGLES = ±2° | | TR. BY | SCALE NONE |
| | | CHK. BY | DATE 2/3/11 |

| CATALOG NUMBER | DESCRIPTION | "L" LENGTH |
|----------------|---|------------|
| CEXT111MFL01 | EXT CABLE. 1/1/1 (1 HOT, 1 NEUTRAL, 1 GROUND), MALE TO FEMALE | 1-FT. |
| CEXT111MFL05 | | 5-FT. |
| CEXT111MFL10 | | 10-FT. |
| CEXT111MFL15 | | 15-FT. |
| CEXT111MFL20 | | 20-FT. |
| CEXT111MFL25 | | 25-FT. |
| CEXT111MFL30 | | 30-FT. |