


M-11907 2

GENERAL INFORMATION			
WIRE LOCATION	WIRE	WIRE COLOR	WIRE SIZE (AWG)
1	LINE (L3)	BLUE	#12
2	ISOLATED GROUND (IG)	GREEN/YELLOW	#12
3	GROUND (G)	GREEN	#12
4	NEUTRAL (N2)	GRAY	#10
5	NEUTRAL (N1)	WHITE	#10
6	LINE (L1)	BLACK	#12
7	LINE (L2)	RED	#12
8	LINE (L4)	PINK	#12

NOTES:
 1. RATING: 20A 120/208 VAC.
 2. ALL DIMENSIONS ARE IN INCH [mm]
 EXCEPT THE FLEXIBLE METAL CONDUIT LENGTH IN FOOT.

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
FEMALE CONNECTOR	THERMOPLASTIC	GRAY
CONDUIT	GALV. STEEL	
CLAMP	STEEL	ZINC PLATE
RIVET	STEEL	ZINC PLATE
INSULATOR	THERMOPLASTIC	
WIRE	COPPER	
FITTING	CAST ALUM.	



REPAIRABLE <input type="checkbox"/>	NON-REPAIRABLE <input checked="" type="checkbox"/>
-------------------------------------	--

2	ADDED FITTING PER DCN #21027	02/06/15
1	NEW RELEASE PER DCN #20674	04/15/14
SYM	REVISIONS	APP DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
 MODULAR WIRING
 EXTENDER CABLE 4/2/2
 FEMALE TO OPEN WIRE

CATALOG NUMBER	DESCRIPTION	"A" LENGTH
CEXT442FWL01	EXT CABLE, 4/2/2 (4 HOTS, 2 NEUTRALS, 2 GROUNDS), FEMALE TO OPEN	12"
CEXT422FWL01XP	EXT CABLE, 4/2/2 (4 HOTS, 2 NEUTRALS, 2 GROUNDS), FEMALE TO OPEN	18"

TOLERANCES UNLESS OTHERWISE SPECIFIED	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT	
.XX = ±.01	DR. BY DMP	APP. BY
.XXX = ±.005	TR. BY DL	SCALE NONE
ANGLES = ±2°	CHK. BY	DATE 2/3/11

DIMENSION SHEET FOR CAT. NO. SEE TABLE REPAIRABLE NON-REPAIRABLE B M-11907 2