

M-11870 2

GENERAL INFORMATION


WIRE LOCATION	WIRE	WIRE COLOR	WIRE SIZE (AWG)
1	LINE (L3)	BLUE	#12
2	ISOLATED GROUND (IG)	GREEN/YELLOW	#12
3	GROUND (G)	GREEN	#12
4	NEUTRAL (N2)	GRAY	#10
5	NEUTRAL (N1)	WHITE	#10
6	LINE (L1)	BLACK	#12
7	LINE (L2)	RED	#12
8	LINE (L4)	PINK	#12

NOTES:

1. RATING: 20A 120/208 V.
2. ALL DIMENSIONS ARE IN INCH [mm] EXCEPT THE FLEXIBLE METAL CONDUIT LENGTH IN FOOT.

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
MALE CONNECTOR	THERMOPLASTIC	GRAY
FEMALE CONNECTOR	THERMOPLASTIC	GRAY
CONDUIT	GALV. STEEL	
CLAMP	STEEL	ZINC PLATE
RIVET	STEEL	ZINC PLATE
INSULATOR	THERMOPLASTIC	
WIRE	COPPER	



DIMENSION SHEET FOR CAT. NO.

SEE TABLE

REPAIRABLE  NON-REPAIRABLE

B

M-11870

2

SYM	REVISIONS	APP	DATE
2	UPDATE PRINT PER DCN #21027		02/06/15
1	NEW RELEASE PER DCN #20674		05/08/14

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE MODULAR WIRING EXTENDER CABLE 4/2/2 MALE TO FEMALE	
TOLERANCES UNLESS OTHERWISE SPECIFIED .XX = ±.01 .XXX = ±.005 ANGLES = ±2°	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT DR. BY DMP APP. BY TR. BY DL SCALE NONE CHK. BY DATE 2/3/11

CATALOG NUMBER	DESCRIPTION	"L" LENGTH
CEXT422MFL01	EXT CABLE, 4/2/2 (4 HOTS, 2 NEUTRALS, 2 GROUNDS), MALE TO FEMALE	1-FT.
CEXT422MFL05		5-FT.
CEXT422MFL10		10-FT.
CEXT422MFL15		15-FT.
CEXT422MFL20		20-FT.
CEXT422MFL25		25-FT.
CEXT422MFL30		30-FT.