



CATALOG NO.	COLOR	CONFIGURATION	RATING
CR5252IG	ORANGE	NEMA 5-15R 	15A, 125V
CR5352IG	ORANGE	NEMA 5-20R 	20A, 125V

DESCRIPTION	MATERIAL	FINISH
TOP	NYLON POLYESTER	SEE CHART
BASE	POLYESTER	BLACK
CONT. SP. BIND. PLATE	.031 BRASS	
GR. CONTACT SP.	.031 BRASS	
INSULATOR	NYLON	NATURAL
WIRE CLAMP	.062 CRS	NICKEL PL.
BRIDGE	.050 STEEL	
GROUND SPRING	.010 STEEL	ZINC PL.
GR BINDING PLATE	BRASS	
BINDING SCREWS	BRASS	*
HEX HD BIND. SC.	BRASS	GREEN
MOUNTING SCREW	STEEL	ZINC PL.
WASHER	FIBER	RED
RIVET	BRASS	

* - WHITE FINISH ON NEUTRAL PARTS WHEN USED

SYM	REVISIONS	APP	DATE
2	CONVERTED ALL DIMS TO 3 PL DECIMAL & TOL ADDED, VIEWS REV'D TO SHOW TRI-DRIVE SCREWS, PER DCN #7773. AMZ DB		7-13-00
1	RELEASED PER DCN 5395		8-28-97

DIMENSION SHEET FOR CAT. NO. SEE TABLE

REPAIRABLE NON-REPAIRABLE

B

M-7798

2

TITLE
 3 WIRE GROUNDING
 DUPLEX STRAIGHT BLADE RECEPTACLE
 WITH ISOLATED GROUND

TOLERANCES UNLESS OTHERWISE SPECIFIED
 FRACTIONS ± 1/64
 DECIMALS ± .005
 ANGLES ± 2°

HARVEY HUBBELL, INC.
 BRIDGEPORT, CONN.
 DR. BY *RM* APP. BY *TCH*
 TR. BY _____ SCALE *1:1*
 CHK'D. BY *TC* DATE *8-28-97*