





DIMENSIONED

CATALOG NO.	RATING	CONDUCTOR & CABLE RANGE	UL	CSA	PSE
CS6364L	50A 125/250V	8/3+10/1 TO 4/4 .83-1.25 [21.1-31.8]	YES	YES	NO
CS8364L	50A 250V 3Ø		YES	YES	NO




CS8364L

- NOTES: UNLESS OTHERWISE SPECIFIED
1. DIMENSIONS IN INCHES [mm]
 2. TOLERANCES: ±.1

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
HOUSING	NYLON	
CONTACT HOLDER	NYLON	
CONTACT COVER	NYLON	
NUT	PBT	
GUIDE PIN	STEEL	NICKEL
DUST SHIELD	RUBBER	
CONTACTS	BRASS	
ASSY RIVETS	BRASS	
DIVIDER	POLY CARBONATE	
TERMINALS	ALUMINUM	TIN
TERMINAL SCREWS	STEEL	TIN
ASSY SCREWS	STEEL	ZINC
GROUND CONTACT	BRASS	
GROUND SHUNT	BRASS	



CATALOG NO. CS6364L
NOT SHOWN TO SCALE

6	REDRAWN WITH EMBEDDED CAD MODEL WITH NO CHANGES TO PART GEOMETRY. PER DCN 21895 SPN	DJP	2/5/16
REV	DESCRIPTION	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
CONNECTOR

TOLERANCES UNLESS OTHERWISE SPECIFIED				WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT			
.XX =	± .01	DR. BY	PJT	APP. BY	MAM		
.XXX =	± .005	TR. BY		SCALE	1:2		
ANGLES =	± 2'	CHK. BY	TLS	DATE	12/23/08		

DIMENSION SHEET FOR CAT. NO.
SEE TABLE

REPAIRABLE ☐

NON-REPAIRABLE ☐

B

M-10799

6