


M-8891 2



- 1 CABLE (YELLOW) 12/3 AWG 300V MIN. 105° C DRY 60° C WATER RESISTANT TYPE SJEOW UL LISTED FOR U.S. AND EITHER CUL LISTED OR CSA CERTIFIED FOR CANADA. CORD TO BE COILED AND TIED WITH 8" I.D.
- 2 NEMA 5-15R MOLDED CONNECTOR (BLACK) WITH TOP AND BOTTOM SURFACES TEXTURED AND MOLDED IN THUMB GRIP.

CAT. NO.	RESET TYPE	VOLTAGE	AMP	WATTS	Hz	CORD (FT) LENGTH
GFP2CM	MANUAL	120V	15	1800	60	2
GFP2CA	AUTOMATIC	120V	15	1800	60	2
GFP25CM	MANUAL	120V	15	1800	60	25
GFP25CA	AUTOMATIC	120V	15	1800	60	25

DESCRIPTION	MATERIAL	FINISH
GFCI BODY	POLYCARB.	BLACK
GFCI BLADES	BRASS	NONE
RESET BUTTON	POLYCARB.	GREEN
TEST BUTTON	POLYCARB.	BLUE
STRAIN RELIEF	ELASTOMER	BLACK
SCREWS	STEEL	TIN-ZINC
CORD GRIP	POLYCARB.	BLACK
CORD	PVC	YELLOW
RECEPTACLE	PVC	BLACK

SYM	REVISIONS	APP	DATE
2	4/7/04 REVISED VIEWS & CALLOUTS TO AGREE WITH NEW DESIGN; ADDED NOTES 1 & 2 PER DCN 11630 RCM SC	SL SL	4/7/04
1	8.2.02 INITIAL RELEASE PER DCN 10077 SM	S.M.	8.23.02

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE GFCI - 15A PLUG SINGLE TAP WITH CORD SET CUSTOMER DWG.

TOLERANCES UNLESS OTHERWISE SPECIFIED	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT	
FRACTIONS ±1/64	DR. BY S.M	APP. BY S.M
DECIMALS ±.005	TR. BY	SCALE NONE
ANGLES ±2°	CHK'D BY S.M	DATE 8.23.02

DIMENSION SHEET FOR CAT. NO. REPAIRABLE  NON-REPAIRABLE  B M-8891 2