


M-9094 2



(2) HUBBELL SHC 1038CR
3/4" CORD RANGE .75 -.88.

CAT. NUMBER	CABLE LENGTH	RATING
GFP-3305	6 FEET	120/240VAC MANUAL
GFP-3315	6 FEET	120/240VAC AUTOMATIC
GFP-5305	6 FEET	250VAC MANUAL 3 PHASE
GFP-5315	6 FEET	250VAC AUTOMATIC 3 PHASE
GFP-4305	6 FEET	120/208VAC MANUAL 3 PHASE
GFP-4315	6 FEET	120/208VAC AUTOMATIC 3 PHASE
GFP-3303	50 FEET	120/240VAC MANUAL

DESCRIPTION	MATERIAL	FINISH

SYM	REVISIONS	APP	DATE
2	ADDED CABLE LENGTH COLUMN TO TABLE; ADDED "GFP-3303" TO TABLE; REVISED "A LOAD" & "B LINE" CALLOUT PER DCN 13367 RCM	JPP	9/1/06
1	INITIAL RELEASE PER DCN. 10717	SM	

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
PORTABLE GFCI 30A SPLIT PHASE & 3 PHASE CIRCUIT GUARD SERIES MANUAL/AUTOMATIC WITH CORD

TOLERANCES UNLESS OTHERWISE SPECIFIED FRACTIONS ± 1/64 DECIMALS ± .005 ANGLES ± 2'	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT	
	DR. BY TJV	APP. BY SM
	TR. BY	SCALE 1:2
	CHK'D BY SM	DATE 5-13-03