





# M-10194 | 1



**NOTES: (UNLESS OTHERWISE SPECIFIED):**

- 1) DIMENSIONS ARE: INCHES [MM]
- 2) SUPPLIED ASSEMBLED WITH: KNURL NUT AND HEX NUT.
- 3) RECOMMENDED PANEL MOUNT OPENING 0.50 [12.7].
- 4) RATING: 10 AMP, 277VAC  
20 AMP, 125VAC  
3/4 HP, 125-250



CATALOG NO.	TERMINAL TYPE	SWITCH DESCRIPTION
HBL11SPM	SPADE, .250 MALE TAB NEMA	SINGLE POLE, SINGLE THROW, MOMENTARY
HBL11M	SCREW, #6-32UNS-2B	SINGLE POLE, SINGLE THROW, MOMENTARY

**LIST OF PARTS**

DESCRIPTION	MATERIAL	FINISH

DIMENSION SHEET FOR CAT. NO. SEE TABLE

REPAIRABLE  NON-REPAIRABLE

B

M-10194

1

1	RELEASED FOR PRODUCTION PER DCN # 13193. JMN	JPP	8/17/06
SYM	REVISIONS	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE  
TOGGLE SWITCH  
SINGLE POLE, SINGLE THROW

TOLERANCES UNLESS OTHERWISE SPECIFIED FRACTIONS ±1/64 DECIMALS ±.005 ANGLES ±2°	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT	
	DR. BY JMN	APP. BY JPP
	TR. BY	SCALE NONE
	CHK'D BY JPP	DATE 8/17/06