







M-6402 4



CORD CLAMP TAKES  
CABLES FROM .300 TO .655  
[7.62] [16.64]

CAT. NUMBER	CONFIGURATION	RATING
HBL1547	NEMA 5-15R NON-LOCKING 	15A 125V
HBL1533	NEMA 5-20R NON-LOCKING 	20A 125V
HBL2547	NEMA L5-15R LOCKING 	15A 125V

NOTES: (UNLESS OTHERWISE SPECIFIED):

1) DIMENSIONS ARE: INCHES  
[MM]

2) XX TOLERANCE TO BE ±.03 [0.76]

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
BODY	NYLON	NATURAL
RETAINER	POLY-CARBONATE	AMBER
WIRE CLAMP	.062 C.R.S.	NICKEL PLATE
CONTACT SPRING	.031 BRONZE	
BINDING SCREW	BRASS	**
GR HEX HD BIND'G SCR	BRASS	GREEN
SPACER	NYLON	YELLOW
OUTER SLEEVE	VINYL	YELLOW
CORD CLAMPS	NYLON	YELLOW

\*\* WHITE FINISH ON NEUTRAL

SUPERSEDES DRAWING DATED 5/3/84

SYM	REVISIONS	APP	DATE
4	IN TABLE, CAT. NO. HBL2547 WAS HBL1247. PER DCN 19814 DDL	DJP	05/13/13
3	ADDED NOTES 1 & 2, IN LIST OF PARTS, WIRE CLAMP WAS ZINC PLATED, "SEE TABLE" WAS "SEE CHART". ADDED "DUST TIGHT" TO DRAWING TITLE. IN CALL-OUT, [7.62] WAS [7.6] AND [16.64] WAS [16.6] PER DCN # 13355. JMN	DJP	11/9/06
2	REDRAWN ON CAD WITH CHANGES; REVISED VIEWS TO AGREE WITH CURRENT PARTS; REVISED SCREWS TO TRI-DRIVE [40.9] WAS [26] PER DCN 11421. RCM	DVB	2/4/04

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE 2 POLE 3 WIRE  
ELASTOMERIC CONNECTORS  
(DUST TIGHT)

TOLERANCES UNLESS OTHERWISE SPECIFIED		WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT	
FRACTIONS	±1/64	DR. BY	AZ
DECIMALS	+0.005	APP. BY	DJP
ANGLES	±2°	TR. BY	RCM
		SCALE	1:1
		CHK'D BY	DJP
		DATE	2/4/04

DIMENSION SHEET FOR CAT. NO. M-6402 4  
 REPAIRABLE  NON-REPAIRABLE