




M-5685 7



ALL SCREWS ARE COMBINATION PHILLIPS/SLOTTED HEAD (CN DEVICES ARE ROBERTSON/SLOTTED)



CAT. NO. (BLACK COVER)	CAT. NO. (GRAY COVER)	CAT. NO.	CONFIGURATION	RATING
	2616 F	2616	NEMA L5-30R.	30A. 125V.
2626CN	2626 F	2626	NEMA L6-30R.	30A. 250V.
		2636	NEMA L7-30R.	30A. 277V.
		2646	NEMA L8-30R.	30A. 480V.
		2656	NEMA L9-30R.	30A. 600V.

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
BODY	NYLON	NATURAL
RETAINER	LEXAN	CLEAR
CASING	NYLON	NATURAL
WIRE CLAMP	.080 C.R.S.	NICKEL PL.
OUTER SPRING	.040 BRASS	
INNER SPRING	.031 BRASS	
TERMINAL SCREWS	BRASS	*
HEX. HD. TERMINAL SCR.	BRASS	GREEN

* WHITE FINISH ON NEUTRAL SCREW WHEN USED.

7	NUMEROUS CHANGES, SEE RECORD PRINT PER DCN 4114. DJG.	JZ	6-13-96
6	DELETED "LISTED PART 231A" FROM RATING PAD & ADDED C-BORES TO SCREW HOLES PER DCN #2901. J.M.J.	JCA	7/28/94
5	6-3-91 CHANGED 2 3/4 DIA. DIM. IN REVISION #4 TO 2 3/16 AJL		6-3-91
4	CHANGED WIRE CLAMP FINISH FROM ZINC PL. TO NICKEL PL. 2 3/4 DIA. WAS 2 1/16 DIA.	CB	AJL 11-28-90
3	UPDATED SIDE & BACK VIEW TO SHOW WIRE FUNNELS DIM. 2 7/32 1/32 WAS 1 5/16 AJL	CEB	2-14-89
2	CAT. NO. 2656 ADDED AJL		7-13-76
1	CASING MATL. WAS LEXAN AJL		3-15-76
SYM	REVISIONS	APP	DATE

TITLE
30A. 2-POLE 3-WIRE
TWIST-LOCK OUTLETS

TOLERANCES UNLESS OTHERWISE SPECIFIED		HARVEY HUBBELL, INC.	
FRACTIONS	± 1/64	BRIDGEPORT, CONN.	
DECIMALS	± .005	DR. BY C.J.G.	APP. BY
ANGLES	± 2°	TR. BY	SCALE FULL
		CHK'D. BY	DATE 6-14-73