


M-64747

COLOR RATING RING  
SEE COLOR CHART



CAT. NO.	CONFIGURATION	RATING	RATING RING COLOR
HBL2710 HBL2710RT	NEMA L14-30R	30A. 125/250 V.	ORANGE
HBL2720 HBL2720RT	NEMA L15-30R	30A 250V. 3Ø	BLUE
HBL2730 HBL2730RT	NEMA L16-30R	30A. 480V. 3Ø	RED
HBL2740	NEMA L17-30R	30A. 600V 3Ø	---
HBL2750	NEMA L18-30R	30V. 120/208V. 3ØY	BLUE
HBL2760	NEMA L19-30R	30V. 277/480V. 3ØY	RED
HBL2770	NEMA L20-30R	30V. 347/600V. 3ØY	---

NOTES

- CATALOG NUMBERS WITH SUFFIX "RT" ARE CSA CERTIFIED AND UL RECOGNIZED FOR USE WITH RING TERMINALS. OR SIDE WIRED.
- CONDUCTOR RANGE #14 AWG TO #8 AWG
- INCHES [mm]
- DEVICES WITH SUFFIX "RT" DO NOT HAVE WIRE GUIDES. AND SCREWS ARE PACKED SEPARATELY IN POLYBAG.

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
BASE	POLYESTER	TAN
COVER	NYLON	BLACK
CONTACT SPRINGS	.040 BRASS	
WIRE CLAMP	.040 BRASS	
GR. SHUNT	.015 BRASS	
BACK PLATE	.040 BRASS	
BINDING SCREWS	BRONZE *	
HEX. HD. SCREW	BRONZE	GREEN
RIVET	BRASS	
END PLATE	.050 BRASS	

SYM	REVISIONS	APP	DATE
7	NOTE 4 ADDED "SCREWS ARE PACKAGED SEPARATELY IN POLYBAG" PER DCN 12307 SPN	RDK	4/11/05
6	ADDED SIDE WIRE AND NO WIRE GUIDE INFORMATION TO NOTES. PER DCN#11361 GDR	RDK	12/8/03
5	ADDED HBL2710RT, HBL 2720RT AND HBL2730RT TO TABLE, ADDED NOTES 1-3, ADDED [mm] DIMS PER DCN10718 MYA	RDK	4/23/03
4	CONVERTED DIMS TO 3 PL DECIMAL VIEW REVISED TO SHOW TRI-DRIVE SCREWS PER DCN #772 AMZ DB		6-30-00
3	ADDED HBL TO CAT # 7252 AM	M/A	10-3-99
2	GR. SHUNT WAS GR. CLAMP; BRASS CONTACT WAS BRASS	A.L.	1-26-90
1	CONTACT SPRING MTL. WAS .040 BRASS 4.31		8-6-86

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE  
30A. 3-POLE 4-WIRE  
TWIST-LOCK RECEPTACLES

TOLERANCES UNLESS OTHERWISE SPECIFIED  
FRACTIONS ± 1/64  
DECIMALS ± .005  
ANGLES ± 2°

WIRING DEVICE DIVISION  
HARVEY HUBBELL, INC.  
BRIDGEPORT, CONN.  
DR. BY A. J. L. APP. BY  
TR. BY SCALE 1:1  
CHK'D BY DATE 1-17-86

DIMENSION SHEET FOR CAT. NO. SEE TABLE  
 REPAIRABLE  NON-REPAIRABLE   
 B M-64747