


M-8260 2



NOTES: (UNLESS OTHERWISE SPECIFIED)

1) DIMENSION FORMAT IS: INCHES  
[ mm ]

AMPS	POLES AND WIRES	MAX VOLTAGE AC/DC	STYLE	CONNECTOR CATALOG NUMBER
30	2P3W	600/250	S1	HBL330PS1WR
30	3P4W	600/250	S1	HBL430PS1WR
30	4P5W	600/250	S1	HBL530PS1WR
30	2P3W	600/250	S2	HBL330PS2WR
30	3P4W	600/250	S2	HBL430PS2WR

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
BOX TERMINAL	STEEL	NICKEL PLATE
GROUND STANDOFF	BRASS	
GROUND BRACKET	COPPER ALLOY	NICKEL PLATE
O-RING	RUBBER	
PINS	BRASS	
CLAMP NUT	BRASS	NICKEL PLATE
CAP GLAND	PET	
CLAMP	PET	
GLAND	RUBBER	
LOCK COLLAR	ALUMINUM	GRAY EPOXY
SHROUD	ALUMINUM	
SET SCREW	STAIN STEEL	
SCREWS	STAIN STEEL	
INTERIOR	THERMOSET POLYESTER	
PLUG BODY	THERMOPLASTIC POLYESTER	

CABLE DIA.  
.360 MIN.  
[ 9 ]  
.780 MAX.  
[ 20 ]

2	ADDED TABLE, "SEE TABLE", AND NOTE 1; DRAWING TITLE WAS "30A PIN & SLEEVE REVERSE PLUG ASSEMBLY STYLES 1 & 2"; REMOVED "MM" FROM DIMENSIONS; PER DCN #8895. JMN	TCM	1/24/02
1	NEW RELEASE PER DCN 7013 RTK	RDK	8/23/99
SYM	REVISIONS	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE  
30A INSULGRIP PIN & SLEEVE REVERSE SERVICE PLUG STYLES 1 & 2

TOLERANCES UNLESS OTHERWISE SPECIFIED		WIRING DEVICE-KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT	
FRACTIONS ± 1/64	3DECIMALS ± .005	DR. BY RTK	APP. BY RDK
ANGLES ± 2°	2DECIMALS ± .01	TR. BY	SCALE 1:1
		CHK'D BY RDK	DATE 8/23/99

DIMENSION SHEET FOR CAT. NO. SEE TABLE

REPAIRABLE

NON-REPAIRABLE

B

M-8260

N