





M-5968 3



CORD RANGE: .220-.660 [5.5-16.5]  
 TYPE: 18/3-16/3 SV, SJ, S  
 14/3 SJ, S  
 12/3 S

NOTES:  
 1. ALL DIMENSIONS TO BE INCHES.  
 [mm]

CATALOG NO.	HOUSING COLOR	DEVICE SCREWS
HBL4723VY	YELLOW	COMBO
HBL4723VYCN		ROBERTSON
HBL4723VBK	BLACK	COMBO
HBL4723VBKCN		ROBERTSON

CODE 74545

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
HOUSING	NYLON	SEE TABLE
CONTACT BLADES	BRASS	1-WHITE
WIRE CLAMPS	STEEL	NICKEL PL.
BINDING SCREWS	STEEL	1-WHITE 1-COPPER
HEX BIND'G SCREW	STEEL	GREEN
CORD CLAMP SCREW	STEEL	YELL. CHRO.
INSERT	(PPO) NORYL	

DIMENSION SHEET FOR CAT. NO. SEE TABLE

REPAIRABLE  NON-REPAIRABLE

SYM	REVISIONS	APP	DATE
3	ADDED TABLE; REVISED CORD CLAMP CALLOUT; ADDED NOTE 1; CONVERTED ALL DIMS. TO DECIMAL/METRIC; REVISED TITLE PER DCN 11902 RCM	JPP	1/26/05
2	REVISED PICTURE OF SCREWS TO TRI-DRIVE DCN 7978 RCM	DB	11/21/00
1	ADDED (3) CAT NOS, REMOVED YELLOW FROM HOUSING FINISH; INSERT MATL WAS BLACK PPHOX PER DCN #9699. J.M.A.	MB	1-20-97

B M-5968

TITLE  
 15A 125V 3 WIRE  
 VALISE TWIST-LOCK PLUG  
 NEMA L5-15P

TOLERANCES UNLESS OTHERWISE SPECIFIED		HARVEY HUBBELL, INC.	
BRIDGEPORT, CONN.		DR. BY ASM APP. BY	
FRACTIONS ± 1/64	DECIMALS ± .005	TR. BY	SCALE FULL
ANGLES ± 2°		CHK'D. BY	DATE 5-11-77

3