





M-8328

1



CORD CLAMP RANGE $\frac{7}{32}$ - $\frac{29}{64}$ DIA. WITH INSERTS
AND $\frac{29}{64}$ - $\frac{21}{32}$ DIA. WITHOUT INSERTS



LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
HOUSING	NYLON	
CONTACT BLADES	BRASS	
WIRE CLAMPS	STEEL	NICKEL PL.
BINDING SCREWS	STEEL	COPPER PL.
HEX BIND'G SCREW	STEEL	GREEN
CORD CLAMP SCRS	STEEL	VELL. CHRO
INSERT	(PPO) NYLON	

DIMENSION SHEET FOR CAT. NO. HBL4773BK, HBL4773V, 5773V, 4773VYCN

REPAIRABLE NON-REPAIRABLE

SYM	REVISIONS	APP	DATE
1	*X* REMOVED; LAST X-REVISION WAS X-0. RELEASED FOR PRODUCTION PER DCN # 7533. JMN	<i>JMN</i>	4-10-00

B

M-8328

TITLE
15A. 27V. 3 WIRE DEAD FRONT VALISE TWIST-LOCK PLUG

TOLERANCES UNLESS OTHERWISE SPECIFIED		HARVEY HUBBELL, INC.	
BRIDGEPORT, CONN.			
FRACTIONS ± 1/64	DR. BY JMN	APP. BY <i>JMN</i>	
DECIMALS ± .005	TR. BY	SCALE F.I.L.L.	
ANGLES ± 2°	CHK'D. BY <i>JMN</i>	DATE 4-10-00	

1

CODE 74545