


M-8264 2



NOTES: (UNLESS OTHERWISE SPECIFIED)
 1) DIMENSION FORMAT IS: INCHES [mm]

CABLE DIA.
 .500 MIN [12]
 1.45 MAX. [36]

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
BOX TERMINAL	STEEL	NICKEL PLATE
GROUND STANDOFF	BRASS	
GROUND BRACKET	COPPER ALLOY	NICKEL PLATE
HINGE BUSHING	ALUMINUM	
SPRING GUIDE	STAIN STEEL	
LID SPRING	STAIN STEEL	
LID	ALUMINUM	GRAY EPOXY
LID LIFTER	ALUMINUM	GRAY EPOXY
O-RING	RUBBER	
LID GASKET	RUBBER	
CLAMP NUT	BRASS	NICKEL PLATE
GLAND	RUBBER	
SPRING WASHER	STAIN STEEL	
WAVE SPRING	STAIN STEEL	
RIVET	ALUMINUM	
CONNECTOR	ALUMINUM	GRAY EPOXY
SET SCREW	STAIN STEEL	
SCREWS	STAIN STEEL	
INTERIOR	THERMOSET POLYESTER	
PLUG BODY	THERMOPLASTIC POLYESTER	
PIN SPRING	COPPER ALLOY	SILVER COATED
SLEEVES	BRASS	

DIMENSION SHEET FOR CAT. NO. SEE TABLE

REPAIRABLE NON-REPAIRABLE

2	ADDED COLUMNS "AMPS", "MAX VOLTAGE AC/DC", & "CONNECTOR CATALOG NUMBER" TO TABLE, "SEE TABLE", AND NOTE 1; DRAWING TITLE WAS "60A PIN & SLEEVE REVERSE CONN. ASSEMBLY STYLES 1 & 2"; REMOVED "MM" FROM DIMENSION; PER DCN #8695.	TCM	1/24/02
1	NEW RELEASE PER DCN 7013 RTK	RDK	8/23/99
SYM	REVISIONS	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE 60A PIN & SLEEVE REVERSE SERVICE CONNECTOR STYLE 1 & 2

TOLERANCES UNLESS OTHERWISE SPECIFIED		WIRING DEVICE-KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT	
FRACTIONS ± 1/64	3DECIMALS ± .005	DR. BY RTK	APP. BY RDK
ANGLES ± 2'	2DECIMALS ± .01	TR. BY	SCALE N/A
		CHK'D BY RDK	DATE 8/23/99

AMPS	MAX VOLTAGE AC/DC	CONNECTOR CATALOG NUMBER	CONNECTOR			DIM "A"		DIM "B"	
			STYLE	POLE	WIRE	INS.	mm	INS.	mm
60	600/250	HBL360CS1WR	S1	2P	3W	9.9	251	3.5	89
60	600/250	HBL460CS1WR	S1	3P	4W				
60	600/250	HBL360CS2WR	S2	2P	3W				
60	600/250	HBL560CS1WR	S1	4P	5W	10.1	256	3.8	96
60	600/250	HBL460CS2WR	S2	3P	4W				

B

M-8264

2