


M-3345 13



CATALOG NO.	DIA.	LENGTH	COLOR	DETAILS
HBL6023	1 27/32	2 23/32	BLACK	A-F
HB_60CM23	1 27/32	2 23/32	YELLOW	A-F
HBL6024	2 19/32	3 29/32	BLACK	E-F
HBL60CM24	2 19/32	3 29/32	YELLOW	E-F
HBL6027	2 1/2	4 5/32	BLACK	A-F
HBL6028	3 1/32	5 19/32	BLACK	E-3
6031	2 5/16	3 15/32	BLACK	A-F
60CM31	2 5/16	3 15/32	YELLOW	A-F
HBL60CM31V	2 5/16	3 15/32	YELLOW	A-F
6032	3 1/32	4 13/16		
60CM32	3 1/32	4 13/16	YELLOW	E-F
HBL60CM32V	3 1/32	4 13/16	YELLOW	E-F
60CM33P	3 1/8	2 5/16	YELLOW	C-F
HB_60CM33V	3 1/8	2 5/16	YELLOW	C-F
HBL60CM33VP	3 1/8	2 5/16	YELLOW	C-F
6035	2 5/8	3 5/8	BLACK	A-F
60CM35	2 5/8	3 5/8	YELLOW	A-F
6036	3 13/32	5 1/32	BLACK	E-F
60CM36	3 13/32	5 1/32	YELLOW	E-F

CATALOG NO.	DIA.	LENGTH	COLOR	DETAILS
HBL7440V	13/8	1 7/8	BLACK	E-D
PH7440	13/8	1 7/8	YELLOW	A-B
HBL7459V	17/32	2 5/32	BLACK	E-D
HBL7490V	17/32	1 15/32	BLACK	A-D
HBL7495V	13/8	2 1/8	BLACK	A-D
PH7499	13/8	2 3/8	YELLOW	A-B
HBL77CM15	2 5/8	5 3/8	YELLOW	C-F-G
HBL77CM16	2 5/8	5 5/16	YELLOW	A-F-G
HBL77CM17	2 5/8	6 5/16	YELLOW	A-F-G
HBL77CM15X	2 5/8	5 3/8	YELLOW	C-F-G
HB_77CM15WX	2 5/8	5 3/8	WHITE	C-F-G
HBL77CM15W	2 5/8	5 3/8	WHITE	C-F-G
HBL77CM16W	2 5/8	5 1/16	WHITE	A-F-G

SUPERSEDES DRAWING DATED 7/2/69

SYM	REVISIONS	APP	DATE
13	REMOVED HBL6031, HBL60CM31, HBL6032, HBL60CM32, HBL60CM33, HBL6035, HBL60CM35, HBL6036, HBL60CM36. ADDED HBL77CM15W AND HBL77CM16W PER DCN 19654. MYA	DJP	2/28/13
12	ADDED HB_77CM15WX PER DCN 19621 SPN	DJP	2-1-12
11	UPDATED TABLE TO AGREE WITH CURRENT "HBL" CAT. NOS.; REMOVED NON "HBL" CAT. NOS.; ADDED HBL77CM15X PER DCN 16514 RCM	DLI	5/28/10

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE.

TITLE  
ELASTOMERIC SEAL-TITE COVERS

TOLERANCES UNLESS OTHERWISE SPECIFIED FRACTIONS ± 1/64 DECIMALS ± .005 ANGLES ± 2°	WIRING DEVICE DIVISION <b>HARVEY HUBBELL, INC.</b> BRIDGEPORT, CONN. DR. BY <u>AWL</u> APP. BY <u>AWL</u> TR. BY <u>AWL</u> SCALE <u>1:1</u> CHK'D. BY <u>AWL</u> DATE <u>2-8-89</u>
---	---

CODE 74545

DIMENSION SHEET FOR CAT. NO. SEE LIST  
 REPAIRABLE  NON-REPAIRABLE   
 M-3345 13