




M-12834

2



HBL6MGRPT6 SHOWN.



NOTE:  
MEETS UL STANDARD 2930  
ALL MODELS ARE EQUIPPED WITH TAMPER RESISTANT HG RECEPTACLES.

CATALOG#	DESCRIPTION	CORD LENGTH	RATING
HBL6MGRPT6	15A UL HCOA RPT 6' CORD	6 FT	15A 125V
HBL6MGRPT15	15A UL HCOA RPT 15' CORD	15 FT	15A 125V
HBL6MGRPT620	20A UL HCOA RPT 6' CORD	6 FT	20A 125V
HBL6MGRPT1520	20A UL HCOA RPT 15' CORD	15 FT	20A 125V

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
BASE	GALV STEEL	WHITE POWDERCOAT
MAIN ENCLOSURE	GALV STEEL	WHITE POWDERCOAT
POWER CORD	THERMOPLASTIC	WHITE
BASE SCREWS	S. STEEL	N/A
SCREWS	STEEL	ZINC
HG DUPLEX RECEPTACLE	THERMOPLASTIC	WHITE
OUTLET COVERS	THERMOPLASTIC	
GROUND SCREW	S. STEEL	N/A
HEX NUTS	STEEL	ZINC
KNURLED NUT	S. STEEL	-
SCREW	S. STEEL	-

2	PRODUCT DESCRIPTIONS UPDATED; EQUIP. GR. TERM. WAS RETURN GR. TERM. .32 WAS .35. ADDED NOTES. DRAWING TITLE REVISED. PER DCN#22739	EMD	11/11/16
1	RELEASED PER DCN# 21618	EMD	8/3/15
SYM	DESCRIPTION	APPRO	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE  
HCOA POWER TAP

TOLERANCES UNLESS OTHERWISE SPECIFIED	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT	
FRACTIONS ±1/64	DR. BY EMD	APP. BY
DECIMALS ±.005	TR. BY	SCALE 1/2
ANGLES ±2°	CHK'D BY	DATE 8/3/2015

DIMENSION SHEET FOR CAT. NO.

REPAIRABLE  NON-REPAIRABLE

B

M-12834

2